

# Model: Drum and container pump for flammable liquids

## Order number: 1.97.870

Correct use: Storage equipment and accessories



for highly flammable hydrocarbons drum pump set consisting of: stainless steel drum pump residue draining pump made from stainless steel, 2 m solvent hose DN 25 conductive hose connections, equipotential bonding cable brass extracton nozzle and PP drum adapter degree of protection IP 54 230 V motor with 5 m cable, earthing pin plug explosion-proof in accordance with the Atex 100a guidelines electrical drive immersion depth: 1000 mm immersion tube Dia: 41 mm

Category: Pump systems Gross weight [kg]: 14,50, Net weight [kg]: 14,50,