

Model: Exhaust air monitor with ventilator

Order number: 2.00.320-1

Correct use: Ventilation of safety cabinets & Exhaust systems



Exhaust air monitor with ventilator

- ATEX-compliant CE Ex II (3) G [c IIB T4], zone 2 in the air flow
- Consisting of:
 - Cage made of sheet steel
 - in silver with sparkling effect
 - Integrated, modern LED-Display "Blue Mode".
 - Plug-in access to the 230V / 50 Hz power supply
 - via IEC-60320 C13 appliance-side connector
 - AC ventilator integrated
 - Optical and acoustic warning in case of errors.
 - Two floating contacts (max. 24V/2A)
 - Noise level Lp5A 34 - 56 dB (A)

Functions:

- Monitoring of the air flow and power supply.
- Internal storage accumulator supplies the monitoring systems for 4 hours in the event of a power failure, display with basic error scale.
- Last 50 alarm messages will be saved
- Air stream flow rate adjustable (21-72 m³/h).
- Low noise.

Category:

Exhaust air systems

Outer width [mm]:

260

Outer depth [mm]:	310
Outer height [mm]:	275
Net weight [kg]:	15,00