

# Model: Exhaust air monitor with ventilator

## Order number: 2.00.320-1

Correct use: Ventilation of safety cabinets & Exhaust systems



### Exhaust air monitor with ventilator

- ATEX-compliant CE Ex II (3) G [c IIB T4], zone 2 in the air flow
- Consisting of:
  - Cage made of sheet steel
  - in silver with sparkling effect
  - Integrated, modern LED-Display "Blue Mode".
  - Plug-in access to the 230V / 50 Hz power supply
  - via IEC-60320 C13 appliance-side connector
  - AC ventilator integrated
  - Optical and acoustic warning in case of errors.
  - Two floating contacts (max. 24V/2A)
  - Noise level Lp5A 34 - 56 dB (A)

#### Functions:

- Monitoring of the air flow and power supply.
- Internal storage accumulator supplies the monitoring systems for 4 hours in the event of a power failure, display with basic error scale.
- Last 50 alarm messages will be saved
- Air stream flow rate adjustable (21-72 m<sup>3</sup>/h).
- Low noise.

Category: Exhaust air systems Outer height [mm]: 275, Outer width [mm]: 260, Outer depth [mm]: 310, Gross weight [kg]: 16,00, Net weight [kg]: 15,00,