

Model: Exhaust air monitor with ventilator

Order number: 2.00.320-1

Correct use: Ventilation of safety cabinets & Exhaust systems



Exhaust air monitor with ventilator

- ATEX-compliant CE Ex II (3) G [c IIB T4], zone 2 in the air flow
- Consisting of:
- Cage made of sheet steel
- in silver with sparkling effect
- Integrated, modern LED-Display "Blue Mode".
- Plug-in access to the 230V / 50 Hz power supply
- via IEC-60320 C13 appliance-side connector
- AC ventilator integrated
- Optical and acoustic warning in case of errors.
- Two floating contacts (max. 24V/2A)
- Noise level Lp5A 34 - 56 dB (A)

Functions:

- Monitoring of the air flow and power supply.
- Internal storage accumulator supplies the
- monitoring systems for 4 hours in the event of a
- power failure, display with basic error scale.
- Last 50 alarm messages will be saved
- Air stream flow rate adjustable (21-72 m³/h).
- Low noise.

Category: Exhaust air systems Outer height [mm]: 275, Outer width [mm]: 255, Outer depth [mm]: 310, Gross weight [kg]: 16,00, Net weight [kg]: 15,00,