

Model: Exhaust air monitor without ventilator

Order number: 2.00.360

Correct use: Ventilation of safety cabinets & Exhaust systems



Exhaust air monitor without ventilator

- ATEX-compliant CE Ex II (3) G [c IIB T4], zone 2 in the air flow
- Consisting of:
- Cage made of sheet steel
- in silver with sparkling effect
- Integrated, modern LED-Display "Blue Mode".
- Plug-in access to the 230V / 50 Hz power supply
- via IEC-60320 C13 appliance-side connector
- AC ventilator integrated
- Optical and acoustic warning in case of errors.
- Two floating contacts (max. 24V/2A)

Functions:

- Monitoring of the air flow and power supply.
- Internal storage accumulator supplies the
- monitoring systems for 4 hours in the event of a
- power failure, display with basic error scale.
- Last 50 alarm messages will be saved

Category: Exhaust air systems Outer height [mm]: 215, Outer width [mm]: 210, Outer depth [mm]: 210, Gross weight [kg]: 5,00, Net weight [kg]: 2,00,