

Model: Pipe penetration for stainless steel pipes, cables and hoses

Order number: 29-70000-048

Correct use: Passive storage



Installation tested for following cabinet models: CLASSIC XL, XS, L, LL, ML, M, S, SL: 29-HHBBTu-xyz, u=5,7 COMPACT XXL, LL, ML: 29-20BB7u-xyz, u=7 BATTERY: 69-HHBBT7-xyz BENCH S, ST: 29-08066u-xyz, u=7,9 BASIC: 23-HHBBTu-xyz, u=0,4,5 UTS ergo: 29-06BBTu-xyz, u=7,9 To be mounted by the customer in order to pass through the cabinet: pipes, cables and tubes Outer dimensions: 120 x 120 x 34 (W x D x H) Usable surface: 80 x 80 Colour: RAL7035 For installation position and max. diameter of penetration see installation manual. No liability in case the installation manual is not adhered to.

Category: Equipment Gross weight [kg]: 2,00, Net weight [kg]: 2,00,