

**Model: VisiCon stainless steel moistener,
capacity: 2 l
Order number: 4.10.021**

Correct use: Safety containers and cleaning containers



Stainless steel 1.4571 (AISI 316Ti) polished Dimensions: approx. 120 x 333 mm (dia x H) without
screw cap. Flame arrester in container neck, Markin prepared according to GefStoffV including
soaking tray with flame arrester and pump tube stainless steel 1.4301

Category:	Cleaning containers
Outer height [mm]:	333
Net weight [kg]:	2,50