

# **Model: Polyethylene canister capacity: 10 l**

## **Order number: 5.09.010**

Correct use: Safety containers and cleaning containers



Polyethylene canister, capacity: 10 l black, electrostatically conductive Dimensions: 300 x 200 x 258 (L x W x H mm) Filler dia: 56 mm Tight closure, type approved receptacle meets ADR / RID / IMDG coding / ICAO-TI. Canister marking according to GefStoffV and BGV A8 Testings: Quality control according to RAL-RG 726/1, BAM-permission Note: In order to guarantee the tight closure of the receptacle, screw down with a turning moment of 20 Nm. For this we recommend the usage of special pliers item code 5.09.003.

Category: for liquid hazardous substances Outer height [mm]: 258, Outer width [mm]: 300, Outer depth [mm]: 195, Gross weight [kg]: 1,50, Net weight [kg]: 0,90,