

**Model: POLYETHYLENE CANISTER black,  
electrostatically  
Order number: 5.09.030**

Correct use: Safety containers and cleaning containers



conductive. Ordering details / dimensions: 364 x 240 x 455 (L x W x H mm) Capacity: ca. 30 Litres  
Filler dia: 56 mm Tried, tested construction, certified receptacles meet ADR / RID / IMDG condong.  
Transportation approval for packaging groups II and III. Collection and transportation according to  
TRbF 143. Test: GS-CERTIFICATE

Category:	for liquid hazardous substances
Outer width [mm]:	364
Outer depth [mm]:	240
Outer height [mm]:	455
Net weight [kg]:	0,90