

Model: Compressor, 6bar low noise, 30dB(A)

Order number: 50-70000-046

Correct use: Supply (active storage)



KOMPRESSOR SILAIR 15D techn. data acc. to manufacturer: max. pressure: 6bar air tank vol.: 4L A/min: 17L power consumption: 0,13kW weight: 20kg with 5m pneumatic hose and pre-assembled connecting parts.

Category: Equipment Outer height [mm]: 440, Outer width [mm]: 220, Outer depth [mm]: 440, Gross weight [kg]: 21,00, Net weight [kg]: 20,00,