

# Model: DISPOSAL LINE

## Order number: 59-060669-035

Correct use: Disposal (active storage)



Classical door technology (push-to-open), door hinge right. For the active storage of flammable liquids. type testing by MPA/TÜV SÜD according to DIN EN 14470-1, DIN EN 14727, EK5/AK4 21-01:2021 and AfPS GS 2019: 01 PAK. Classification of ex-zones according to DIN EN 60079-10. Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD. Construction and colour:

- Outer carcass sheet steel, ELGR conductive
- Doors sheet steel, ELBL conductive
- Inner carcass sheet steel, ELGR conductive ELGR >> similar to RAL 7035 ELBL >> similar to RAL 5010 Fittings and features:
- doors close automatically in case of fire
- doors remain open in any position
- cylinder lock for safe access
- 1 automatically moving-out pull-out tray
- 1 canister guidance for 2 canisters
- 1 integrated object extraction
- 2 canisters, 10 l each,
- 1 waste cap with stopcock and extraction pipe
- 1 pipe penetration with steel pipe
- Electr. conductive corrugated hose (HDPE)
- monitoring unit: exhaust air, level indicator
- exhaust air connection on the cabinet rear
- visual inspection of the ventilation opening
- earthing connection on the cabinet rear
- interior fittings grounded to carcass
- base with slots for floor extraction, RAL 7015 Further technical information:  
[www.dueperthal.com](http://www.dueperthal.com)

Category: Type 90 - flammable liquids Model size: pro S, Model type: U (Under-bench cabinet),

Outer height [mm]: 631, Outer width [mm]: 601, Outer depth [mm]: 593, Gross weight [kg]: 130,00, Net weight [kg]: 130,00, Equipment package: 10 litres, Number of storage levels: 1, Number of storage areas per storage level: 1, Door operation: push-to-open door technology, Door technology: wing door technology,