

Model: COMPLEX LINE

Order number: 59-200975-007

Correct use: Supply (active storage)



one-hand door technology (door handle). For the active storage of flammable liquids. type testing by MPA/TÜV SÜD according to DIN EN 14470-1, DIN EN 14727, EK5/AK4 09-10:2009 and AfPS GS 2014: 01 PAK. Classification of ex-zones according to DIN EN 60079-10. Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD. Construction and colour:

- Outer carcass sheet steel, ELGR conductive
- Doors sheet steel, ELBL conductive
- Inner carcass sheet steel, ELGR conductive ELGR >> similar to RAL 7035 ELBL >> similar to RAL 5010
- Fittings and features:
 - doors close automatically in case of fire
 - doors remain open in any position
 - cylinder lock for safe access
- 1 bottom tray sheet steel, ELGR conductive
- 1 hot-dip galvanised grating
- 1 filling station with integrated extraction
- electr. conductive corrugated hoses (HDPE)
- compresses air connection on the cabinet top
- exhaust air monitoring unit
- exhaust air connection on the cabinet top
- visual inspection of the ventilation opening
- earthing connection on the cabinet top
- interior fittings grounded to carcass
- adjustable feet for level adjustment

- set-back base, RAL 7015

Category:	Type 90 - flammable liquids
Model size	LL
Model type	STANDARD (storage shelves)
Outer width [mm]:	894
Outer depth [mm]:	747
Outer height [mm]:	2.085
Net weight [kg]:	500,00
Equipment package	with exhaust air monitoring unit and ventilator
Number of storage levels	2
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology