

Model: COMPLEX LINE

Order number: 59-200975-017

Correct use: Supply (active storage)



one-hand door technology (door handle). For the active storage of flammable liquids. Type testing by MPA according to DIN EN 14470-1. Tested according to DIN EN 16121 and DIN EN 16122, Mark of approval: CE mark Construction and colour:

- all steel sheets with conductive coating
- outer carcass sheet steel, similar to RAL 7035
- doors sheet steel, similar to RAL 5010
- Inner carcass sheet steel, similar to RAL 7035
- Fittings and features:
- doors close automatically in case of fire
- doors remain open in any position
- cylinder lock for safe access
- bottom tray sheet steel, similar to RAL 7035
- hot-dip galvanised grating
- filling station
- PE Air Operated Diaphragm Pump 3/8"
- PTFE and stainless steel sheathed hoses
- compressed air connection on the cabinet roof
- exhaust air monitoring with ventilation unit
- exhaust air connection on the cabinet roof
- visual inspection of the ventilation opening
- earthing connection on the cabinet top
- interior fittings grounded to carcass
- adjustable feet for level adjustment

- set-back base, RAL 7015

Category: Type 90 - flammable liquids Model size: LL, Model type: STANDARD (storage shelves), Outer height [mm]: 2.085, Outer width [mm]: 894, Outer depth [mm]: 747, Gross weight [kg]: 442,00, Net weight [kg]: 442,00, Equipment package: with exhaust air monitoring unit and ventilator, Number of storage levels: 1, Number of storage areas per storage level: 1, Door operation: one-hand wing door technology, Door technology: wing door technology,