

Model: BATTERY LINE

Order number: 69-130667-070

Correct use: Storage of batteries



Classical door technology (door handle), door hung right For storage and charging of lithium-ion batteries Type-tested by MPA/ TÜV SÜD according to DIN EN 14470-1, DIN EN 16121, DIN EN 16122, DIN 31000, and IEC 61439 Loss prevention in terms of VdS 3103 Mark of approval: Safety tested and CE mark Construction and colour:

- Outer carcass sheet steel, RAL 7035
- Door sheet steel, PANTONE 389 C
- Inner carcass decor panels, RAL 7035
- Load adapter (tested), RAL 7035
- Fittings and features:
 - Door remains open in any position
 - Door closes automatically in case of fire
 - Cylinder locks for access security
 - Backdraftlock after inside fire
- Bottom tray sheet steel, RAL 7035
- 3 storage levels sheet steel, RAL 7035
- 1 storage area per storage level
- 4 sockets per storage area
- Exhaust air connection on the cabinet roof
- Visual inspection of the ventilation opening
- Earthing connection on the cabinet roof
- Interior fittings grounded to carcass
- Adjustable feet for level adjustment
- Set-back base, RAL 7015
- Plug ready connection to a power supply
- connectiontype: CEE L+N+PE 6h
- Further technical information:
 - www.dueperthal.com

Category:	Type 90 - lithium ion batteries
Model size	S
Model type	STATION (sockets)
Outer width [mm]:	594
Outer depth [mm]:	612
Outer height [mm]:	1.385
Net weight [kg]:	230,00
Supply voltage	single-phase 230V/50Hz
Equipment package	without signal transmission
Number of storage levels	3
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology