

Model: BATTERY LINE

Order number: 69-200667-070

Correct use: Storage of batteries



Classical door technology (door handle), door hung right For storage and charging of lithium-ion batteries Type-tested by MPA/ TÜV SÜD according to DIN EN 14470-1, DIN EN 16121, DIN EN 16122, DIN 31000, and IEC 61439 Loss prevention in terms of VdS 3103 Mark of approval: Safety tested and CE mark Construction and colour:

- Outer carcass sheet steel, RAL 7035
>
- Door sheet steel, PANTONE 389 C
>
- Inner carcass decor panels, RAL 7035
>
- Load adapter (tested), RAL 7035
>
- Fittings and features:
>
- Door remains open in any position
>
- Door closes automatically in case of fire
>
- Cylinder locks for access security
>
- Backdraftlock after inside fire
>
- Bottom tray sheet steel, RAL 7035
>

- 4 storage levels sheet steel, RAL 7035
>
- 1 storage area per storage level
>
- 4 sockets per storage area
>
- Exhaust air connection on the cabinet roof
>
- Visual inspection of the ventilation opening
>
- Earthing connection on the cabinet roof
>
- Interior fittings grounded to carcass
>
- Adjustable feet for level adjustment
>
- Set-back base, RAL 7015
>
- Plug ready connection to a power supply
>
- connectiontype: CEE L+N+PE 6h
>
- Further technical information:
>
- www.dueperthal.com
>

Category: Type 90 - lithium ion batteries Model size: M, Model type: STATION (sockets), Outer height [mm]: 2.085, Outer width [mm]: 594, Outer depth [mm]: 612, Gross weight [kg]: 320,00, Net weight [kg]: 320,00, Supply voltage: single-phase 230V/50Hz, Equipment package: without signal transmission, Number of storage levels: 4, Number of storage areas per storage level: 1, Door operation: classical technology, Door technology: wing door technology,