

Model: BATTERY LINE

Order number: 69-201267-032

Correct use: Storage of batteries



Classical door technology (door handle) For the storage of lithium-ion batteries Type-tested by MPA/ TÜV SÜD according to DIN EN 14470-1, DIN EN 16121, DIN EN 16122, and DIN 31000 Loss prevention in terms of VdS 3103:2015-06 Mark of approval: Safety tested and CE mark
Construction and colour:

- Outer carcass sheet steel, RAL 7035
- Doors sheet steel, PANTONE 389 C
- Inner carcass decor panels, RAL 7035 Fittings and features:
- Doors remain open in any position
- Doors close automatically in case of fire
- Cylinder locks for access security
- Backdraftlock after inside fire
- bottom tray sheet steel, RAL 7035
- 4 storage levels sheet steel, RAL 7035
- 2 storage area per storage level
- exhaust air connection on the cabinet roof
- visual inspection of the ventilation opening
- earthing connection on the cabinet roof
- interior fittings grounded to carcass
- adjustable feet for level adjustment
- set-back base, RAL 7015 more technical information: www.dueperthal.com

Category: Type 90 - lithium ion batteries Outer height [mm]: 2.045, Outer width [mm]: 1.194, Outer depth [mm]: 612, Gross weight [kg]: 530,00, Net weight [kg]: 530,00, Model size: XL, Model type: STANDARD, Door technology: wing door technology, Door operation: classical technology, Number of storage areas per storage level: 2, Number of storage levels: 4,