

# Model: SUPREME LINE

## Order number: 79-130660-021

Correct use: Compressed gas cylinders indoor storage



Classical door technology (door handle), door hung right. For the storage of pressurised gas cylinders. Type testing by MPA/TÜV SÜD according to DIN EN 14470-2, DIN EN 16121 and DIN EN 16122, EK5/AK4 09-10:2009 and AfPS GS 2014:01 PAK Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD Construction and colour:

- Outer carcass sheet steel, RAL 7035
  - Door sheet steel, RAL 3003
  - Inner carcass of decor panels, RAL 7035 Fittings and features:
  - Cylinder lock for safe access
  - Roll-in flap with pitch
  - Cylinder holder incl 2 retaining belts
  - Fitting holder
  - Exhaust air connection socket on the cabinet roof
- Further technical information:  
[www.dueperthal.com](http://www.dueperthal.com)

Category: Type G90 - storage of gas Model size: S, Outer height [mm]: 1.415, Outer width [mm]: 595, Outer depth [mm]: 610, Gross weight [kg]: 260,00, Net weight [kg]: 260,00, Number of storage levels: 1, Number of storage areas per storage level: 1, Door operation: classical technology, Door technology: wing door technology,