

Model: SUPREME LINE
Order number: 79-200660-021

Correct use: Compressed gas cylinders indoor storage



Classical door technology (door handle), door hung right. For the storage of pressurised gas cylinders. Type testing by MPA/TÜV SÜD according to DIN EN 14470-2, DIN EN 16121 and DIN EN 16122, EK5/AK4 09-10:2009 and AfPS GS 2014:01 PAK Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD Construction and colour:

- Outer carcass sheet steel, RAL 7035
 - Door sheet steel, RAL 3003
 - Inner carcass of decor panels, RAL 7035 Fittings and features:
 - Cylinder lock for safe access
 - Roll-in flap with pitch
 - Cylinder holder incl 2 retaining belts
 - Fitting holder
 - Exhaust air connection socket on the cabinet roof
- Further technical information:
www.dueperthal.com

Category:	Type G90 - storage of gas
Model size	M
Outer width [mm]:	595
Outer depth [mm]:	610

Outer height [mm]:	2.070
Net weight [kg]:	350,00
Number of storage levels	1
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology