

Model: SUPREME LINE

Order number: 79-201460-021

Correct use: Compressed gas cylinders indoor storage



Classical door technology (door handle). For the storage of pressurised gas cylinders. Type testing by MPA/TÜV SÜD according to DIN EN 14470-2, DIN EN 16121 and DIN EN 16122, EK5/AK4 09-10:2009 and AfPS GS 2014:01 PAK Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD Construction and colour:

- Outer carcass sheet steel, RAL 7035
- Doors sheet steel, RAL 3003
- Inner carcass of decor panels, RAL 7035 Fittings and features:
- Cylinder lock for safe access
- Roll-in flap with pitch
- Cylinder holder incl 4 retaining belts
- Fitting holder
- Exhaust air connection socket on the cabinet roof Further technical information:
www.dueperthal.com

Category:	Type G90 - storage of gas
Model size	XXL
Outer width [mm]:	1.395
Outer depth [mm]:	610
Outer height [mm]:	2.070
Net weight [kg]:	680,00

Number of storage levels	1
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology