

# Model: SUPREME LINE

## Order number: 79-201460-021

Correct use: Compressed gas cylinders indoor storage



Classical door technology (door handle). For the storage of pressurised gas cylinders. Type testing by MPA/TÜV SÜD according to DIN EN 14470-2, DIN EN 16121 and DIN EN 16122, EK5/AK4 09-10:2009 and AfPS GS 2014:01 PAK Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD Construction and colour:

- Outer carcass sheet steel, RAL 7035
- Doors sheet steel, RAL 3003
- Inner carcass of decor panels, RAL 7035 Fittings and features:
- Cylinder lock for safe access
- Roll-in flap with pitch
- Cylinder holder incl 4 retaining belts
- Fitting holder
- Exhaust air connection socket on the cabinet roof Further technical information:  
[www.dueperthal.com](http://www.dueperthal.com)

Category: Type G90 - storage of gas Model size: XXL, Outer height [mm]: 2.070, Outer width [mm]: 1.395, Outer depth [mm]: 610, Gross weight [kg]: 680,00, Net weight [kg]: 680,00, Number of storage levels: 1, Number of storage areas per storage level: 1, Door operation: classical technology, Door technology: wing door technology,