

Model: SUPREME LINE

Order number: 79-201460-021

Correct use: Compressed gas cylinders indoor storage



Classical door technology (door handle). For the storage of pressurised gas cylinders. Type testing by MPA/TÜV SÜD according to DIN EN 14470-2, DIN EN 16121 and DIN EN 16122, EK5/AK4 09-10:2009 and AfPS GS 2014:01 PAK Mark of approval: GS/CE mark, high quality mark of approval by TÜV SÜD Construction and colour:

- Outer carcass sheet steel, RAL 7035
 - Doors sheet steel, RAL 3003
 - Inner carcass of decor panels, RAL 7035 Fittings and features:
 - Cylinder lock for safe access
 - Roll-in flap with pitch
 - Cylinder holder incl 4 retaining belts
 - Fitting holder
 - Exhaust air connection socket on the cabinet roof
- Further technical information:
www.dueperthal.com

Category: Type G90 - storage of gas Model size: XXL, Outer height [mm]: 2.070, Outer width [mm]: 1.395, Outer depth [mm]: 610, Gross weight [kg]: 680,00, Net weight [kg]: 680,00, Number of storage levels: 1, Number of storage areas per storage level: 1, Door operation: classical technology, Door technology: wing door technology,