


**Model: Control unit type A with integrated solenoid valve**  
**Order number: 8.300.01-1**

Correct use: Storage equipment and accessories



with hand-held terminal approved for zone 1 potentially explosive atmospheres Housing made from highly-resistant, impact-resistant polycarbonate with 12 m cable. Dim. (WxDxH): approx. 280 x 280 x 160 mm TÜV-proofed

Category:	DÜANA tank filling system
Outer width [mm]:	280
Outer depth [mm]:	280
Outer height [mm]:	160
Net weight [kg]:	8,00