

# Model: COOL LINE

## Order number: 89-200977-030

Correct use: Cooled storage



Safety cabinet with built-in refrigerator. Interior of refrigerator explosion protected Ex II 3G, Ex nA II T6, SNCH 07, ATEX 0124 X. Temperatures inside from +1 degrees C to +15 degrees C. Refrigerant: R 600a, Voltage: 230 V / 50 Hz Outer dimensions: 895 x 745 x 2080 (WxDxH) mm Inner dimensions: 550 x 430 x 1400 (WxDxH) mm Description: Outer carcass from powder-coated sheet steel in RAL 7035 light grey, door in RAL 9016 traffic white, refrigerator door white. Door with arrest system, thermal monitoring and cylinder lock is automatically closed in case of fire. Refrigerator door is opened/closed separately. Type-tested by MPA/TÜV-SÜD acc. to DIN EN 14470-1, GS/CE mark with exhaust air monitor with ventilation unit 2.00.320C, ATEX conformity, Inner fittings: 5 shelves made from shatterproof glass, 1 bottom tray, 1 perforated sheet insert Base set back, height: 85 mm Please note that the refrigerator will automatically switch off in case of a ventilation system failure.

Category:	Type 90 - refrigerated storage
Model size	XL
Model type	STANDARD (storage shelves)
Outer width [mm]:	894
Outer depth [mm]:	747

Outer height [mm]:	2.085
Net weight [kg]:	499,00
Equipment package	with exhaust air monitoring unit and ventilator
Number of storage levels	6
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology