

# Model: COOL LINE

## Order number: 89-200977-030

Correct use: Cooled storage



Safety cabinet with integrated refrigerators. Refrigerator interiors explosion-proof Ex II 3G, Ex nA II T6, SEV 08 ATEX 0149 X, 2 refrigerators with temperature range from +3 to +16 degrees Celsius. Refrigerant: R 600a, Voltage 230 V/ 50Hz, Outer dimensions: 895 x 745 x 2080 (WxDxH) mm Inner dimensions: 455 x 435 x 669 (WxDxH) mm per refrigerator Description: Outer carcass of powder-coated sheet steel in RAL 7035 light grey, doors in RAL 9016, traffic white, refrigerator doors white, Cabinet door with arrest system, thermocouple and lock cylinder, self-closing in case of fire. Door hung right. Refrigerator doors to be opened and closed separately. Type testing by MPA/TÜV Süd according to DIN EN 14470-1, GS / CE-mark, with exhaust air monitor with ventilator 2.00.320C, ATEX -conform. Interior fittings per refrigerator: 3 shelves made of shatterproof glass 1 bottom tray and 1 perforated sheet insert made of powder-coated sheet steel. Please note: In case of a failure of the ventilation system, the refrigerators will be switched off automatically.

Category: Type 90 - refrigerated storage Model size: XL, Model type: STANDARD (storage shelves), Outer height [mm]: 2.085, Outer width [mm]: 894, Outer depth [mm]: 747, Gross weight [kg]: 499,00, Net weight [kg]: 499,00, Equipment package: with exhaust air monitoring unit and ventilator, Number of storage levels: 6, Number of storage areas per storage level: 1, Door operation: classical technology, Door technology: wing door technology,