

Model: COOL LINE
Order number: 89-200977-040

Correct use: Cooled storage



Safety cabinet with integrated refrigerators. Refrigerator interiors explosion-proof Ex II 3G, Ex nA II T6, SEV 08 ATEX 0149 X, 2 refrigerators with temperature range from +3 to +16 degrees Celsius. Refrigerant: R 600a, Voltage 230 V/ 50Hz, Outer dimensions: 895 x 745 x 2080 (WxDxH) mm Inner dimensions: 455 x 435 x 669 (WxDxH) mm per refrigerator Description: Outer carcass of powder-coated sheet steel in RAL 7035 light grey, doors in RAL 9016, traffic white, refrigerator doors white, Cabinet door with arrest system, thermocouple and lock zylinder, self-closing in case of fire. Door hung right. Refrigerator doors to be opened and closed separately. Type testing by MPA/TÜV Süd according to DIN EN 14470-1, GS / CE-mark, with exhaust air monitor with ventilator 2.00.320C, ATEX -conform. Interior fittings per refrigerator: 3 shelves made of shatterproof glass 1 bottom tray and 1 perforated sheet insert made of powder-coated sheet steel. Please note: In case of a failure of the ventilation system, the refrigerators will be switched off automatically.

Category:	Type 90 - refrigerated storage
Model size	XL
Model type	DUAL (two interiors)
Outer width [mm]:	894
Outer depth [mm]:	747

Outer height [mm]:	2.085
Net weight [kg]:	499,00
Equipment package	with exhaust air monitoring unit and ventilator
Number of storage levels	8
Number of storage areas per storage level	1
Door operation	classical technology
Door technology	wing door technology