

## Model: Safety eye wash for in-wall mounting

### Order number: 9.21.085

Correct use: Emergency showers



Stainless steel ball valve, not self-closing. Push plate made of steel, powder-coated in green. Water-bearing parts made of brass. Including emergency sign (pictogram). Shower heads 45° angled. Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation. Required water connection: ½" internal thread. Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2. Tested and certified acc. to DIN-DVGW.

Category:	Eye showers
Outer width [mm]:	330
Outer depth [mm]:	305
Net weight [kg]:	1,10