

Model: Safety eye wash for surface wall mounting

Order number: 9.30.085

Correct use: Emergency showers



Stainless steel ball valve, not self-closing. Collecting basin made of stainless steel, powder-coated in green. Push plate made of steel, powder-coated in green. Water-bearing parts made of brass. Including emergency sign (pictogram). Water flow rate: 16 l/min. at 1.5 - 5 bar pressure, incl. automatic flow regulation. Required water connection: $\frac{3}{4}$ " external thread. Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2. Tested and certified acc. to DIN-DVGW.

Category: Eye showers Outer width [mm]: 270, Outer depth [mm]: 465, Gross weight [kg]: 3,60, Net weight [kg]: 3,10,