

# Model: Hand-held eye wash for wall/table mounting

## Order number: 9.71.302

Correct use: Emergency showers



incl. impact protection, dust protection cover and emergency sign (pictogram). Shower head 45° angled. Casing made of glass fiber reinforced plastic. Water-bearing parts made of brass. Water flow rate: 7 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer. "Required water connection: 1/2" external thread." Hose length 1500 mm. Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2. Tested and certified acc. to DIN-DVGW.

Category:	Eye showers
Outer width [mm]:	80
Outer depth [mm]:	80
Outer height [mm]:	270
Net weight [kg]:	1,08