

Model: Hand-held eye wash for wall/table mounting

Order number: 9.71.402

Correct use: Emergency showers



incl. impact protection, dust protection cover and emergency sign (pictogram). 2 shower heads 45° angled. Handle with integrated locking trigger made of plastic, valve not self-closing. Casing made of glass fiber reinforced plastic. Water-bearing parts made of brass. Water flow rate: 14 l/min. at 1.5 - 5 bar flow pressure, incl. automatic flow regulation and backflow preventer. Required water connection: ½" external thread. Hose length 1500 mm. Tested acc. to: BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-2. Tested and certified acc. to DIN-DVGW.

Category: Eye showers Outer height [mm]: 310, Outer width [mm]: 150, Outer depth [mm]: 80, Gross weight [kg]: 1,78, Net weight [kg]: 1,28,