

**Model: Body shower, stainless steel, wall  
mounting above door  
Order number: 9.84.095**

Correct use: Emergency showers



Piping, shower arm, ball valve and pull rod made of stainless steel. High-performance shower head made of stainless steel, self-draining. Including emergency sign (pictogram). Water flow rate: 50 l/min. at 1.5 - 3 bar flow pressure, incl. automatic flow regulation. Required water connection: ¾" internal thread. Tested acc. to BGI/GUV-I 850-0, DIN 1988, DIN EN 1717, ANSI Z358.1-2004, DIN EN 15154-1. Tested and certified acc. to DIN-DVGW.

Category:	Body showers
Outer width [mm]:	565
Outer depth [mm]:	500
Net weight [kg]:	2,20